

# SCE-642432SSWS Cut Sheet



Saginaw workstation, NEMA 12/13, 64 x 24 x 32in (HxWxD), freestanding, dual access, 304 stainless steel, #4 brush finish, 2-door, 3-point keylocking flush swing handle, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-642432SSWS>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Saginaw                      |
| <b>Item</b>                         | Workstation                  |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 12/13                        |
| <b>IP Rating</b>                    | IP55                         |
| <b>Nominal Enclosure Dimensions</b> | 64 x 24 x 32in (HxWxD)       |
| <b>Enclosure Height</b>             | 64.00in                      |
| <b>Enclosure Width</b>              | 24.25in                      |
| <b>Enclosure Depth</b>              | 34.39in                      |
| <b>Mounting</b>                     | Freestanding                 |
| <b>Integral Mounting Feet</b>       | No                           |
| <b>Integral Mounting Flange</b>     | No                           |

|                                    |                                       |
|------------------------------------|---------------------------------------|
| <b>Dual Access</b>                 | Yes                                   |
| <b>Knockouts</b>                   | No                                    |
| <b>Bottom Gland Plate</b>          | No                                    |
| <b>Material</b>                    | 304 stainless steel                   |
| <b>Finish</b>                      | #4 brush                              |
| <b>Cover Type</b>                  | 2-door                                |
| <b>Hinge Type</b>                  | Concealed hinges                      |
| <b>Latch Type</b>                  | 3-point keylocking flush swing handle |
| <b>Number of Door Latches</b>      | 2                                     |
| <b>Secondary Latch Type</b>        | 1/4-turn semi-flush latch             |
| <b>Number Of Secondary Latches</b> | 2                                     |
| <b>Shelf</b>                       | No                                    |
| <b>Window Material</b>             | Polycarbonate                         |
| <b>Padlockable</b>                 | No                                    |
| <b>Keylocking</b>                  | Yes                                   |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-642432SSWS.pdf>  
See store item page for other formats.