

SCE-642432WS Cut Sheet



Saginaw workstation, NEMA 12/13, 64 x 24 x 32in (HxWxD), freestanding, dual access, carbon steel, RAL 7035 light gray, powder coat finish, 2-door, 3-point keylocking flush swing handle, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-642432WS>

Technical Specifications

Brand	Saginaw
Item	Workstation
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	12/13
IP Rating	IP55
Nominal Enclosure Dimensions	64 x 24 x 32in (HxWxD)
Enclosure Height	64.00in
Enclosure Width	24.25in
Enclosure Depth	34.39in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	Yes

Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	RAL 7035 light gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	Concealed hinges
Latch Type	3-point keylocking flush swing handle
Number of Door Latches	2
Secondary Latch Type	1/4-turn semi-flush latch
Number Of Secondary Latches	2
Shelf	No
Window Material	Polycarbonate
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-642432WS.pdf>
See store item page for other formats.