

# SCE-65XVR3716 Cut Sheet



Saginaw disconnect enclosure, vented, NEMA 3R, right flange, 65 x 37 x 16in (HxWxD), wall mount, carbon steel, white, powder coat finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-65XVR3716>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>Vented</b>	Yes
<b>NEMA Rating</b>	3R
<b>IP Rating</b>	IP32
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Dimensions</b>	65 x 37 x 16in (HxWxD)
<b>Enclosure Height</b>	65.00in
<b>Enclosure Width</b>	37.38in
<b>Enclosure Depth</b>	17.07in
<b>Mounting</b>	Wall

<b>Integral Mounting Feet</b>	No
<b>Material</b>	Carbon steel
<b>Color</b>	White
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Single-door
<b>Hinge Type</b>	Concealed hinges
<b>Number of Hinges Per Door</b>	3
<b>Latch Type</b>	3-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	Purchase subpanel separately

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-65XVR3716.pdf>  
See store item page for other formats.