

SCE-66ST2626SSWS Cut Sheet



Saginaw workstation, slope top, NEMA 12/13, 66 x 26 x 26in (HxWxD), freestanding, dual access, 304 stainless steel, #4 brush finish, 2-door, 3-point keylocking flush swing handle, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-66ST2626SSWS>

Technical Specifications

Brand	Saginaw
Item	Workstation
Subpanel	Purchase subpanel separately
Slope Top	Yes
3-Piece Assembly	No
Vented	No
NEMA Rating	12/13
IP Rating	IP55
Nominal Enclosure Dimensions	66 x 26 x 26in (HxWxD)
Enclosure Height	65.59in
Enclosure Width	26.00in
Enclosure Depth	28.14in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	Yes
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Concealed hinges
Latch Type	3-point keylocking flush swing handle
Number of Door Latches	2
Secondary Latch Type	1/4-turn semi-flush latch
Number Of Secondary Latches	2
Shelf	No
Window Material	Polycarbonate
Padlockable	No
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-66ST2626SSWS.pdf>
See store item page for other formats.