

SCE-724818SSFSD Cut Sheet



Saginaw enclosure, NEMA 3R/12/13, 72 x 48 x 18in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, double-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-724818SSFSD>

Technical Specifications

Brand	Saginaw	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/12/13	Cover Type	Double-door
IP Rating	IP55	Hinge Type	Concealed hinges
Nominal Enclosure Dimensions	72 x 48 x 18in (HxWxD)	Number of Hinges Per Door	3
Enclosure Height	72.00in	Latch Type	3-point keylocking/padlocking combo handle
Enclosure Width	48.00in	Number Of Latches	1
Enclosure Depth	19.05in	Shelf	No
Mounting	Freestanding	Padlockable	Yes
Integral Mounting Feet	No	Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-724818SSFSD.pdf>
See store item page for other formats.