

SCE-72EL3630SS6FS Cut Sheet



Saginaw Enviroline series enclosure, NEMA 3R/4/4X/12/13, 72 x 36 x 30in (HxWxD), freestanding, 316L stainless steel, #4 brush finish, single-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72EL3630SS6FS>

Technical Specifications

Brand	Saginaw
Item	Enclosure
Series	Enviroline
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	72 x 36 x 30in (HxWxD)
Enclosure Height	72.00in
Enclosure Width	36.00in
Enclosure Depth	31.05in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	316L stainless steel
Finish	#4 brush
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	3
Latch Type	3-point keylocking/padlocking combo handle
Number Of Latches	1
Secondary Latch Type	1/4-turn semi-flush
Number Of Secondary Latches	2
Shelf	No
Padlockable	Yes
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-72EL3630SS6FS.pdf>
See store item page for other formats.