

SCE-72EL6024FSD Cut Sheet



Saginaw Enviroline series enclosure, NEMA 3R/4/12/13, 72 x 60 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72EL6024FSD>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Saginaw |
| Item | Enclosure |
| Series | Enviroline |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/4/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 72 x 60 x 24in (HxWxD) |
| Enclosure Height | 72.00in |
| Enclosure Width | 60.00in |
| Enclosure Depth | 25.05in |
| Mounting | Freestanding |

| | |
|----------------------------------|--|
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | 2-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 3 |
| Latch Type | 3-point keylocking/padlocking combo handle |
| Number Of Latches | 2 |
| Padlockable | Yes |
| Keylocking | Yes |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |