

# SCE-72X7318LP Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 72 x 73 x 18in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72X7318LP>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	3R/12/13
<b>IP Rating</b>	IP55
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Dimensions</b>	72 x 73 x 18in (HxWxD)
<b>Enclosure Height</b>	72.00in
<b>Enclosure Width</b>	73.00in
<b>Enclosure Depth</b>	19.05in
<b>Mounting</b>	Floor
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Material</b>	Carbon steel

<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	2-door
<b>Hinge Type</b>	Concealed hinges
<b>Number of Hinges Per Door</b>	4
<b>Latch Type</b>	3-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	Purchase subpanel separately
<b>For Use With</b>	Most major brand disconnect switches and circuit breakers
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>