

SCE-72XD5418SS Cut Sheet



Saginaw enclosure, NEMA 3R/4/4X/12/13, 72 x 54 x 18in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 2-door, 3-point padlocking handle, external disconnect enclosure included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72XD5418SS>

Technical Specifications

Brand	Saginaw
Item	Enclosure
Slope Top	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	72 x 54 x 18in (HxWxD)
Enclosure Height	72.00in
Enclosure Width	53.75in
Enclosure Depth	19.07in
Mounting	Freestanding
Dual Access	No
Knockouts	No
Material	304 stainless steel

Finish	#4 brush
Cover Type	2-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking handle
Number Of Latches	2
Padlockable	Yes
Keylocking	No
Subpanel	Powder coated subpanel included
Includes	External disconnect enclosure
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement