

SCE-72XEL6112SS6LP Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 72 x 61 x 12in (HxWxD), floor mount, 316L stainless steel, #4 brush finish, 2-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72XEL6112SS6LP>

Technical Specifications

| | |
|-------------------------------------|------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure |
| Series | Enviroline |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/4/4X/12/13 |
| IP Rating | IP66 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 72 x 61 x 12in (HxWxD) |
| Enclosure Height | 72.00in |
| Enclosure Width | 61.00in |
| Enclosure Depth | 13.05in |

| | |
|----------------------------------|------------------------------|
| Mounting | Floor |
| Integral Mounting Feet | No |
| Material | 316L stainless steel |
| Finish | #4 brush |
| Cover Type | 2-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 4 |
| Latch Type | 3-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Purchase subpanel separately |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-72XEL6112SS6LP.pdf>
See store item page for other formats.