

# SCE-72XM2818SS Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 72 x 28 x 18in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, single-door, 3-point padlocking handle, powder coated subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72XM2818SS>

## Technical Specifications

<b>Brand</b>	Saginaw	<b>Mounting</b>	Freestanding
<b>Item</b>	Disconnect enclosure	<b>Integral Mounting Feet</b>	No
<b>Slope Top</b>	No	<b>Material</b>	304 stainless steel
<b>Vented</b>	No	<b>Finish</b>	#4 brush
<b>NEMA Rating</b>	3R/4/4X/12/13	<b>Cover Type</b>	Single-door
<b>IP Rating</b>	IP66	<b>Hinge Type</b>	Concealed hinges
<b>Disconnect Mounting</b>	Right flange	<b>Number of Hinges Per Door</b>	4
<b>Nominal Enclosure Dimensions</b>	72 x 28 x 18in (HxWxD)	<b>Latch Type</b>	3-point padlocking handle
<b>Enclosure Height</b>	72.00in	<b>Padlockable</b>	Yes
<b>Enclosure Width</b>	27.50in	<b>Keylocking</b>	No
<b>Enclosure Depth</b>	19.05in	<b>Subpanel</b>	Powder coated subpanel included

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-72XM2818SS.pdf>  
See store item page for other formats.