

# SCE-72XM3EQ18G Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 72 x 100 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 3-door, 3-point padlocking handle, (2) galvanized subpanels included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72XM3EQ18G>

## Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	3R/12/13
IP Rating	IP55
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	72 x 100 x 18in (HxWxD)
Enclosure Height	72.00in
Enclosure Width	99.50in
Enclosure Depth	19.07in
Mounting	Freestanding

Integral Mounting Feet	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	3-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	(2) galvanized subpanels included

## Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-72XM3EQ18G.pdf>  
See store item page for other formats.