

SCE-72XR6618 Cut Sheet



Saginaw enclosure, NEMA 3R/12/13, 72 x 66 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, external rotary disconnect enclosure included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72XR6618>

Technical Specifications

Brand	Saginaw
Item	Enclosure
Slope Top	No
NEMA Rating	3R/12/13
IP Rating	IP55
Nominal Enclosure Dimensions	72 x 66 x 18in (HxWxD)
Enclosure Height	72.00in
Enclosure Width	65.75in
Enclosure Depth	19.05in
Mounting	Freestanding
Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray

Finish	Powder coat
Cover Type	2-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking handle
Number Of Latches	2
Padlockable	Yes
Keylocking	No
Subpanel	Powder coated subpanel included
Includes	External rotary disconnect enclosure
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement