

SCE-84XM3EW18SS6 Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 84 x 118 x 18in (HxWxD), freestanding, 316L stainless steel, #4 brush finish, 3-door, 3-point padlocking handle, (2) powder coated subpanels included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-84XM3EW18SS6>

Technical Specifications

| | |
|-------------------------------------|-------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/4/4X/12/13 |
| IP Rating | IP66 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 84 x 118 x 18in (HxWxD) |
| Enclosure Height | 84.00in |
| Enclosure Width | 117.50in |
| Enclosure Depth | 19.05in |

| | |
|----------------------------------|--------------------------------------|
| Mounting | Freestanding |
| Integral Mounting Feet | No |
| Material | 316L stainless steel |
| Finish | #4 brush |
| Cover Type | 3-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 4 |
| Latch Type | 3-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | (2) powder coated subpanels included |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-84XM3EW18SS6.pdf>
See store item page for other formats.