

SCE-84XM3EW24G Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 84 x 118 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 3-door, 3-point padlocking handle, (2) galvanized subpanels included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-84XM3EW24G>

Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	3R/12/13
IP Rating	IP55
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	84 x 118 x 24in (HxWxD)
Enclosure Height	84.00in
Enclosure Width	117.50in
Enclosure Depth	25.07in
Mounting	Freestanding
Dual Access	No
Knockouts	No
Material	Carbon steel

Color	ANSI 61 gray
Finish	Powder coat
Cover Type	3-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	(2) galvanized subpanels included
For Use With	Most major brand disconnect switches and circuit breakers
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-84XM3EW24G.pdf>
See store item page for other formats.