

SCE-84XM3EW24SS Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 84 x 118 x 24in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 3-door, 3-point padlocking handle, (2) powder coated subpanels included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-84XM3EW24SS>

Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	84 x 118 x 24in (HxWxD)
Enclosure Height	84.00in
Enclosure Width	117.50in
Enclosure Depth	25.05in

Mounting	Freestanding
Integral Mounting Feet	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	3-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	(2) powder coated subpanels included

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-84XM3EW24SS.pdf>
See store item page for other formats.