

# SCE-84XM5EW24SS6 Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 84 x 197 x 24in (HxWxD), freestanding, 316L stainless steel, #4 brush finish, 5-door, 3-point padlocking handle, (3) powder coated subpanels included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-84XM5EW24SS6>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Disconnect enclosure
<b>Slope Top</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	3R/4/4X/12/13
<b>IP Rating</b>	IP66
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Height</b>	84in
<b>Nominal Enclosure Width</b>	196.75in
<b>Nominal Enclosure Depth</b>	25.07in
<b>Mounting</b>	Freestanding
<b>Material</b>	316L stainless steel

<b>Finish</b>	#4 brush
<b>Cover Type</b>	5-door
<b>Hinge Type</b>	Concealed hinges
<b>Number of Hinges Per Door</b>	4
<b>Latch Type</b>	3-point padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No
<b>Subpanel</b>	(3) powder coated subpanels included
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-84XM5EW24SS6.pdf>  
See store item page for other formats.