

# SCE-84XM7824G Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 84 x 78 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, galvanized subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-84XM7824G>

## Technical Specifications

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Brand</b>                        | Saginaw                |
| <b>Item</b>                         | Disconnect enclosure   |
| <b>Slope Top</b>                    | No                     |
| <b>Vented</b>                       | No                     |
| <b>NEMA Rating</b>                  | 3R/12/13               |
| <b>IP Rating</b>                    | IP55                   |
| <b>Disconnect Mounting</b>          | Right flange           |
| <b>Nominal Enclosure Dimensions</b> | 84 x 78 x 24in (HxWxD) |
| <b>Enclosure Height</b>             | 84.00in                |
| <b>Enclosure Width</b>              | 77.75in                |
| <b>Enclosure Depth</b>              | 25.07in                |
| <b>Mounting</b>                     | Freestanding           |

|                                  |                              |
|----------------------------------|------------------------------|
| <b>Integral Mounting Feet</b>    | No                           |
| <b>Material</b>                  | Carbon steel                 |
| <b>Color</b>                     | ANSI 61 gray                 |
| <b>Finish</b>                    | Powder coat                  |
| <b>Cover Type</b>                | 2-door                       |
| <b>Hinge Type</b>                | Concealed hinges             |
| <b>Number of Hinges Per Door</b> | 4                            |
| <b>Latch Type</b>                | 3-point padlocking handle    |
| <b>Padlockable</b>               | Yes                          |
| <b>Keylocking</b>                | No                           |
| <b>Subpanel</b>                  | Galvanized subpanel included |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-84XM7824G.pdf>  
See store item page for other formats.