

SCE-90SMP14 Cut Sheet



Saginaw subpanel, side mount, carbon steel, white, powder coat finish. For use with 90in (H) x min. 18in (D) Saginaw freestanding enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-90SMP14>

Technical Specifications

| | |
|--|--|
| Brand | Saginaw |
| Item | Subpanel |
| Subpanel Type | Side mount |
| Height | 78in |
| Width | 14in |
| Thickness | 11 gauge |
| Material | Carbon steel |
| Color | White |
| Finish | Powder coat |
| Perforations accept self-tapping screws for mounting lightweight components | No |
| For Use With | 90in (H) x min. 18in (D) Saginaw freestanding enclosures |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |