

SCE-90SMP14 Cut Sheet



Saginaw subpanel, side mount, carbon steel, white, powder coat finish. For use with 90in (H) x min. 18in (D) Saginaw freestanding enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-90SMP14>

Technical Specifications

Brand	Saginaw
Item	Subpanel
Subpanel Type	Side mount
Height	78in
Width	14in
Thickness	11 gauge
Material	Carbon steel
Color	White

Finish	Powder coat
Perforations accept self-tapping screws for mounting lightweight components	No
For Use With	90in (H) x min. 18in (D) Saginaw freestanding enclosures

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-90SMP14.pdf>
See store item page for other formats.