

# SCE-90XD4EW18 Cut Sheet



Saginaw enclosure, NEMA 3R/12/13, 90 x 158 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 4-door, 3-point padlocking handle, external disconnect enclosure included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-90XD4EW18>

## Technical Specifications

|                          |              |
|--------------------------|--------------|
| Brand                    | Saginaw      |
| Item                     | Enclosure    |
| Slope Top                | No           |
| NEMA Rating              | 3R/12/13     |
| IP Rating                | IP55         |
| Nominal Enclosure Height | 90in         |
| Nominal Enclosure Width  | 158in        |
| Nominal Enclosure Depth  | 18in         |
| Mounting                 | Freestanding |
| Dual Access              | No           |
| Knockouts                | No           |
| Material                 | Carbon steel |
| Color                    | ANSI 61 gray |

|                           |                                                                                                                   |
|---------------------------|-------------------------------------------------------------------------------------------------------------------|
| Finish                    | Powder coat                                                                                                       |
| Cover Type                | 4-door                                                                                                            |
| Hinge Type                | Concealed hinges                                                                                                  |
| Number of Hinges Per Door | 4                                                                                                                 |
| Latch Type                | 3-point padlocking handle                                                                                         |
| Number Of Latches         | 4                                                                                                                 |
| Padlockable               | Yes                                                                                                               |
| Keylocking                | No                                                                                                                |
| Subpanel                  | (2) powder coated subpanels included                                                                              |
| Includes                  | External disconnect enclosure                                                                                     |
| Additional Information    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                      |                                                                     |
|----------------------|---------------------------------------------------------------------|
| UL Listed File #     | E69392                                                              |
| UL Recognized File # | None                                                                |
| UL Hazardous File #  | None                                                                |
| CE                   | None                                                                |
| CSA File #           | None                                                                |
| RoHS Status          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH             | <a href="#">View EU REACH document</a>                              |
| Other                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-90XD4EW18.pdf>  
See store item page for other formats.