

SCE-90XM4024G Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 90 x 40 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point padlocking handle, galvanized subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-90XM4024G>

Technical Specifications

| | |
|-------------------------------------|------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/12/13 |
| IP Rating | IP55 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 90 x 40 x 24in (HxWxD) |
| Enclosure Height | 90.00in |
| Enclosure Width | 39.50in |
| Enclosure Depth | 25.07in |
| Mounting | Freestanding |

| | |
|----------------------------------|------------------------------|
| Integral Mounting Feet | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 4 |
| Latch Type | 3-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Galvanized subpanel included |

Agency Approvals

| | |
|-----------------------------|---------------------------------------------------------------------|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-90XM4024G.pdf>
See store item page for other formats.