

SCE-90XM7824SS Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 90 x 78 x 24in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 2-door, 3-point padlocking handle, powder coated subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-90XM7824SS>

Technical Specifications

Brand	Saginaw	Mounting	Freestanding
Item	Disconnect enclosure	Integral Mounting Feet	No
Slope Top	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/4/4X/12/13	Cover Type	2-door
IP Rating	IP66	Hinge Type	Concealed hinges
Disconnect Mounting	Right flange	Number of Hinges Per Door	4
Nominal Enclosure Dimensions	90 x 78 x 24in (HxWxD)	Latch Type	3-point padlocking handle
Enclosure Height	90.00in	Padlockable	Yes
Enclosure Width	77.75in	Keylocking	No
Enclosure Depth	25.05in	Subpanel	Powder coated subpanel included

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-90XM7824SS.pdf>
See store item page for other formats.