SCE-924B Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Saginaw operator console, NEMA 3R/12/13, 48 x 24 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking/padlocking combo handle, handle hasp.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/SCE-924B

Technical Specifications

Brand	Saginaw
Item	Operator console
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/12/13
IP Rating	IP55
Nominal Enclosure Height	48in
Nominal Enclosure Width	24in
Nominal Enclosure Depth	18in
Mounting	Freestanding
Integral Mounting Flange	No
Dual Access	No
Material	Carbon steel

Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Number of Lid Hinges	2
Latch Type	3-point keylocking/padlocking combo handle
Number of Door Latches	1
Secondary Latch Type	1/4-turn semi-flush latch
Number Of Secondary Latches	2
Padlockable	Yes
Padlock Attachment Type	Handle hasp
Keylocking	Yes

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/SCE-924B.pdf
See store item page for other formats.