SCE-AC1870B120VSS6 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

Saginaw Enviro-Therm air conditioner, 1870 BTU/H, R-134a or R-513a, 115 VAC operating voltage, 316 stainless steel housing, side mount. For use with NEMA/UL Type 3R, 4, 4X & 12 enclosures.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/SCE-AC1870B120VSS6

Technical Specifications

Brand	Saginaw
Series	Enviro-Therm
Item	Air conditioner
Nominal Cooling Capacity	1870 BTU/H
Operating Voltage	115 VAC
Frequency	50/60 Hz
Running Current	5.6A
Refrigerant	R-134a or R-513a
Height	32.68in
Width	12.00in
Depth	10.63in

Mounting	Side
Filter-Free	No
Filter Size	11.34 x 9.45in
Housing Material	316 stainless steel
IP Rating	IP56
For Use With	NEMA/UL Type 3R, 4, 4X & 12 enclosures
Includes	Washable/reusable filter, mounting template, and hardware
Dangerous Goods	• Packaging Instructions: 200 • UN Number: 3159 • Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	E498756
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/SCE-AC1870B120VSS6.pdf
See store item page for other formats.