

SCE-AC2550B460VSS Cut Sheet



Saginaw Enviro-Therm air conditioner, 2550 BTU/H, R-134a, 460 VAC operating voltage, 304 stainless steel housing, side mount. For use with NEMA/UL Type 3R, 4, 4X & 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-AC2550B460VSS>

Technical Specifications

Brand	Saginaw
Series	Enviro-Therm
Item	Air conditioner
Nominal Cooling Capacity	2550 BTU/H
Operating Voltage	460 VAC
Frequency	50/60 Hz
Running Current	2.1A
Refrigerant	R-134a
Height	32.68in
Width	12.00in
Depth	10.63in
Mounting	Side
Filter-Free	No
Filter Size	11.34 x 9.45in
Housing Material	304 stainless steel
IP Rating	IP56
For Use With	NEMA/UL Type 3R, 4, 4X & 12 enclosures
Includes	Washable/reusable filter, mounting template, and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	E498756
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document