

# SCE-AC5100B120VSS6 Cut Sheet



Saginaw Enviro-Therm air conditioner, 5100 BTU/H, R-134a, 115 VAC operating voltage, 316 stainless steel housing, side mount. For use with NEMA/UL Type 3R, 4, 4X & 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-AC5100B120VSS6>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Series</b>	Enviro-Therm
<b>Item</b>	Air conditioner
<b>Nominal Cooling Capacity</b>	5100 BTU/H
<b>Operating Voltage</b>	115 VAC
<b>Frequency</b>	50/60 Hz
<b>Running Current</b>	14.2A
<b>Refrigerant</b>	R-134a
<b>Height</b>	45.28in
<b>Width</b>	15.55in
<b>Depth</b>	10.63in

<b>Mounting</b>	Side
<b>Filter-Free</b>	No
<b>Filter Size</b>	14.88 x 11.81in
<b>Housing Material</b>	316 stainless steel
<b>IP Rating</b>	IP56
<b>For Use With</b>	NEMA/UL Type 3R, 4, 4X & 12 enclosures
<b>Includes</b>	Washable/reusable filter, mounting template, and hardware
<b>Dangerous Goods</b>	<ul style="list-style-type: none"><li>• Packaging Instructions: 200</li><li>• UN Number: 3159</li><li>• Hazard Type: Compressed Gas</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E498756
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-AC5100B120VSS6.pdf>  
See store item page for other formats.