

SCE-AC8500B120V Cut Sheet



Saginaw Enviro-Therm air conditioner, 8500 BTU/H, R-134a, 115 VAC operating voltage, carbon steel housing, RAL 7035 light gray, side mount. For use with NEMA/UL Type 3R, 4 & 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-AC8500B120V>

Technical Specifications

| | |
|---------------------------------|---|
| Brand | Saginaw |
| Series | Enviro-Therm |
| Item | Air conditioner |
| Nominal Cooling Capacity | 8500 BTU/H |
| Operating Voltage | 115 VAC |
| Frequency | 50/60 Hz |
| Running Current | 16.8A |
| Refrigerant | R-134a |
| Height | 61.02in |
| Width | 18.00in |
| Depth | 13.98in |
| Mounting | Side |
| Filter-Free | No |
| Filter Size | 16.54 x 14.57in |
| Housing Material | Carbon steel |
| Color | RAL 7035 light gray |
| IP Rating | IP56 |
| For Use With | NEMA/UL Type 3R, 4 & 12 enclosures |
| Includes | Washable/reusable filter, mounting template, and hardware |
| Dangerous Goods | <ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E498756 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |