

SCE-EXR18-400 Cut Sheet



Saginaw external rotary disconnect enclosure, 48.00 x 17.00 x 18.00in (HxWxD), carbon steel, ANSI 61 gray, NEMA 3R/12/13. Galvanized subpanel, cable-operated mechanical interlock and mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-EXR18-400>

Technical Specifications

Brand	Saginaw
Item	External rotary disconnect enclosure
Size	48.00 x 17.00 x 18.00in (HxWxD)
Material	Carbon steel
Color	ANSI 61 gray
NEMA Rating	3R/12/13
Includes	Galvanized subpanel, cable-operated mechanical interlock and mounting hardware

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-EXR18-400.pdf>
See store item page for other formats.