


SCE-GB10 Cut Sheet



Saginaw grounding bar, 4in length, (10) #10-32 tapped holes and (2) 9/32in holes.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-GB10>

Technical Specifications

Brand	Saginaw
Item	Grounding bar
Length	4in
Width	1in
Thickness	0.25in
Material	Electro tin plated copper
Grounding Points	(10) #10-32 tapped holes and (2) 9/32in holes

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-GB10.pdf>
See store item page for other formats.