


# SCE-GB10 Cut Sheet



Saginaw grounding bar, 4in length, (10) #10-32 tapped holes and (2) 9/32in holes.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-GB10>

---

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Grounding bar
<b>Length</b>	4in
<b>Width</b>	1in
<b>Thickness</b>	0.25in
<b>Material</b>	Electro tin plated copper
<b>Grounding Points</b>	(10) #10-32 tapped holes and (2) 9/32in holes

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>