

# SCE-L9366ELJSS Cut Sheet

Saginaw wiring trough, 6 x 9 x 36in (HxDxL), NEMA 3R/4/4X/12/13, wall mount, 304 stainless steel, #4 brush finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-L9366ELJSS>



## Technical Specifications

|                                     |                           |
|-------------------------------------|---------------------------|
| <b>Brand</b>                        | Saginaw                   |
| <b>Item</b>                         | Wiring trough             |
| <b>Series</b>                       | Enviroline Junction       |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13             |
| <b>IP Rating</b>                    | IP66                      |
| <b>Nominal Enclosure Dimensions</b> | 9 x 36 x 6in (HxWxD)      |
| <b>Enclosure Height</b>             | 9.00in                    |
| <b>Enclosure Depth</b>              | 6.18in                    |
| <b>Enclosure Length</b>             | 36.00in                   |
| <b>Mounting</b>                     | Wall                      |
| <b>Integral Mounting Feet</b>       | No                        |
| <b>Knockouts</b>                    | No                        |
| <b>Material</b>                     | 304 stainless steel       |
| <b>Finish</b>                       | #4 brush                  |
| <b>Cover Type</b>                   | Single-door               |
| <b>Latch Type</b>                   | 1/4-turn semi-flush latch |
| <b>Padlockable</b>                  | No                        |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |