

SCE-N68L7818SS6 Cut Sheet



Saginaw NextGen series left enclosure bay, NEMA 3R/4/4X/12/13, 68 x 78 x 18in (HxWxD), freestanding, 316 stainless steel, #4 brush finish, 2-door, 3-point padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-N68L7818SS6>

Technical Specifications

Brand	Saginaw
Item	Enclosure bay
Series	NextGen
Subpanel	Purchase subpanel separately
Bay Type	Left
Slope Top	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	68 x 78 x 18in (HxWxD)
Enclosure Height	68.00in
Enclosure Width	77.75in
Enclosure Depth	18.00in
Mounting	Freestanding
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	316 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking combo handle
Number Of Latches	1
Shelf	No
Padlockable	Yes
Keylocking	No
Includes	Gasket and hardware for baying

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-N68L7818SS6.pdf>
See store item page for other formats.