

SCE-N80RX4018SS Cut Sheet



Saginaw NextGen series right disconnect enclosure bay, NEMA 3R/4/4X/12/13, 80 x 40 x 18in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, single-door, 3-point padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-N80RX4018SS>

Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure bay
Series	NextGen
Subpanel	Purchase subpanel separately
Bay Type	Right
Slope Top	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Height	80in
Nominal Enclosure Width	40in
Nominal Enclosure Depth	18in
Mounting	Freestanding
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking combo handle
Number Of Latches	1
Shelf	No
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-N80RX4018SS.pdf>
See store item page for other formats.