

SCE-N80RX7818SS6 Cut Sheet



Saginaw NextGen series right disconnect enclosure bay, NEMA 3R/4/4X/12/13, 80 x 78 x 18in (HxWxD), freestanding, 316 stainless steel, #4 brush finish, 2-door, 3-point padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-N80RX7818SS6>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Saginaw |
| Item | Disconnect enclosure bay |
| Series | NextGen |
| Subpanel | Purchase subpanel separately |
| Bay Type | Right |
| Slope Top | No |
| NEMA Rating | 3R/4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 80 x 78 x 18in (HxWxD) |
| Enclosure Height | 80.00in |
| Enclosure Width | 77.75in |
| Enclosure Depth | 18.00in |
| Mounting | Freestanding |
| Integral Mounting Feet | No |

| | |
|----------------------------------|---------------------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | 316 stainless steel |
| Finish | #4 brush |
| Cover Type | 2-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 4 |
| Latch Type | 3-point padlocking combo handle |
| Number Of Latches | 1 |
| Shelf | No |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E69392 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-N80RX7818SS6.pdf>
See store item page for other formats.