

SCE-N80RX7818 Cut Sheet



Saginaw NextGen series right disconnect enclosure bay, NEMA 3R/4/12/13, 80 x 78 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, polyester powder coat finish, 2-door, 3-point padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-N80RX7818>

Technical Specifications

Brand	Saginaw
Item	Disconnect enclosure bay
Series	NextGen
Subpanel	Purchase subpanel separately
Bay Type	Right
Slope Top	No
NEMA Rating	3R/4/12/13
Nominal Enclosure Dimensions	80 x 78 x 18in (HxWxD)
Enclosure Height	80.00in
Enclosure Width	77.75in
Enclosure Depth	18.00in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Polyester powder coat
Cover Type	2-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	4
Latch Type	3-point padlocking combo handle
Number Of Latches	1
Shelf	No
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E69392
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCE-N80RX7818.pdf>
See store item page for other formats.