

# SCE-NEP8024SS6 Cut Sheet



Saginaw NextGen series side exterior panel, 80 x 24in (HxD), 316 stainless steel, #4 brush finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-NEP8024SS6>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Series</b>	NextGen
<b>Item</b>	Side exterior panel
<b>Height</b>	79in
<b>Depth</b>	23.5in
<b>Material</b>	316 stainless steel
<b>Finish</b>	#4 brush
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	E69392
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-NEP8024SS6.pdf>  
See store item page for other formats.