

# SCE-PWK138NFSS Cut Sheet



Saginaw enclosure window, 13.25 x 8.25in window, UV-resistant polycarbonate, 304 stainless steel, #4 brush finish, oil-resistant gasket. For use with NEMA 4X enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-PWK138NFSS>

## Technical Specifications

|                        |                            |
|------------------------|----------------------------|
| <b>Brand</b>           | Saginaw                    |
| <b>Item</b>            | Enclosure window           |
| <b>Window Size</b>     | 13.25 x 8.25in             |
| <b>Window Material</b> | UV-resistant polycarbonate |
| <b>Frame Material</b>  | 304 stainless steel        |
| <b>Finish</b>          | #4 brush                   |
| <b>Gasket Type</b>     | Oil-resistant              |
| <b>Cutout Size</b>     | 14.69 x 9.69in             |
| <b>For Use With</b>    | NEMA 4X enclosures         |
| <b>Includes</b>        | Mounting hardware          |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None   |
| <b>UL Recognized File #</b> | E69392   |
| <b>UL Hazardous File #</b>  | None   |
| <b>CE</b>                   | None   |
| <b>CSA File #</b>           | None   |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions -<br>No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                                 |
| <b>Other</b>                | <a href="#">RoHS Statement</a>   |