

SCE-PWK138NF Cut Sheet



Saginaw enclosure window, 13.25 x 8.25in window, UV-resistant polycarbonate, carbon steel, ANSI 61 gray, powder coat finish, oil-resistant gasket. For use with NEMA 4 enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-PWK138NF>

Technical Specifications

Brand	Saginaw
Item	Enclosure window
Window Size	13.25 x 8.25in
Window Material	UV-resistant polycarbonate
Frame Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Gasket Type	Oil-resistant
Cutout Size	14.69 x 9.69in
For Use With	NEMA 4 enclosures
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	E69392
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement