

SCE-PWK2315NFSS Cut Sheet



Saginaw enclosure window, 23.25 x 15.25in window, UV-resistant polycarbonate, 304 stainless steel, #4 brush finish, oil-resistant gasket. For use with NEMA 4X enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-PWK2315NFSS>

Technical Specifications

| | |
|------------------------|----------------------------|
| Brand | Saginaw |
| Item | Enclosure window |
| Window Size | 23.25 x 15.25in |
| Window Material | UV-resistant polycarbonate |
| Frame Material | 304 stainless steel |
| Finish | #4 brush |
| Gasket Type | Oil-resistant |
| Cutout Size | 24.69 x 16.69in |
| For Use With | NEMA 4X enclosures |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|---------------------------------------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | E69392 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SCE-PWK2315NFSS.pdf>
See store item page for other formats.