

# SCE-PWK2919NF Cut Sheet



Saginaw enclosure window, 29.25 x 19.25in window, UV-resistant polycarbonate, carbon steel, ANSI 61 gray, powder coat finish, oil-resistant gasket. For use with NEMA 4 enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-PWK2919NF>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Enclosure window
<b>Window Size</b>	29.25 x 19.25in
<b>Window Material</b>	UV-resistant polycarbonate
<b>Frame Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Gasket Type</b>	Oil-resistant
<b>Cutout Size</b>	30.69 x 20.69in
<b>For Use With</b>	NEMA 4 enclosures
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E69392
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-PWK2919NF.pdf>  
See store item page for other formats.