

# SCE-SA310TMJ Cut Sheet



Saginaw suspension arm fitting, top-mount base, 310 degrees movement range, aluminum, RAL 7035 light gray, powder coat finish. For use with 3.54 x 2.56in suspension arm profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-SA310TMJ>

## Technical Specifications

Brand	Saginaw
Item	Suspension arm fitting
Fitting Type	Top-mount base
Movement Range	310 degrees
Material	Aluminum
Color	RAL 7035 light gray
Finish	Powder coat
For Use With	3.54 x 2.56in suspension arm profile

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-SA310TMJ.pdf>  
See store item page for other formats.