

# SCE-SAH230WH Cut Sheet



Saginaw suspension arm fitting, wall-mount base, 230 degrees movement range, aluminum, RAL 7035 light gray, powder coat finish. For use with 5 x 3in suspension arm profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-SAH230WH>

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Suspension arm fitting
<b>Fitting Type</b>	Wall-mount base
<b>Movement Range</b>	230 degrees
<b>Material</b>	Aluminum
<b>Color</b>	RAL 7035 light gray
<b>Finish</b>	Powder coat
<b>For Use With</b>	5 x 3in suspension arm profile

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-SAH230WH.pdf>  
See store item page for other formats.