

# SCE-SAS20J Cut Sheet



Saginaw suspension arm profile, round U-bend, 2.38in OD, 19.69in offset, 304 stainless steel, #4 brush finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-SAS20J>

---

## Technical Specifications

|                 |                        |
|-----------------|------------------------|
| <b>Brand</b>    | Saginaw                |
| <b>Item</b>     | Suspension arm profile |
| <b>Shape</b>    | Round U-bend           |
| <b>Size</b>     | 2.38in OD              |
| <b>Offset</b>   | 19.69in                |
| <b>Material</b> | 304 stainless steel    |
| <b>Finish</b>   | #4 brush               |

---

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-SAS20J.pdf>  
See store item page for other formats.