

# SCE-SAS39S Cut Sheet

Saginaw suspension arm profile, round J-bend, 2.38in OD, 39.37 x 23.62in offset, 304 stainless steel, #4 brush finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-SAS39S>

---

## Technical Specifications

<b>Brand</b>	Saginaw
<b>Item</b>	Suspension arm profile
<b>Shape</b>	Round J-bend
<b>Size</b>	2.38in OD
<b>Offset</b>	39.37 x 23.62in
<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-SAS39S.pdf>  
See store item page for other formats.