


SCM2K4000X12 Cut Sheet



Comepi safety switch, tongue (key) interlock, 90-degree adjustable head, (2) N.C. safety output(s), (1) N.O. monitoring output(s), 62 x 108 x 43mm, die-cast aluminum body, thermoplastic head.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCM2K4000X12>

Technical Specifications

Brand	Comepi
Item	Safety switch
Actuator Type	Tongue (key) interlock
Head Type	90-degree adjustable
Action	Slow action break before make
Safety Output Type	(2) N.C.
Monitoring Output Type	(1) N.O.
Housing Size	62 x 108 x 43mm
Body Material	Die-cast aluminum
Head Material	Thermoplastic
IP Rating	IP66
Connection	(3) 1/2in NPT cable entries
Additional Information	Purchase actuating tongue (key) separately

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document