


SCM2K9900X12 Cut Sheet



Comepi safety switch, cable-pull interlock, with reset, 25m maximum pull cable length, (2) N.C. safety output(s), (1) N.O. monitoring output(s), die-cast aluminum body, thermoplastic head, (3) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCM2K9900X12>

Technical Specifications

Brand	Comepi
Item	Safety switch
Actuator Type	Cable-pull interlock
Reset	Yes
Action	Slow action
Maximum Pull Cable Length	25m
Safety Output Type	(2) N.C.

Monitoring Output Type	(1) N.O.
Housing Size	62 x 165 x 43mm
Body Material	Die-cast aluminum
Head Material	Thermoplastic
IP Rating	IP66
Connection	(3) 1/2in NPT cable entries
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SCM2K9900X12.pdf>
See store item page for other formats.