

SDM2K61W02 Cut Sheet



Comepi safety switch, lever hinge interlock, slow action, (2) N.C. safety output(s), die-cast aluminum body, plastic head, (3) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDM2K61W02>

Technical Specifications

Brand	Comepi
Item	Safety switch
Actuator Type	Lever hinge interlock
Head Type	90-degree adjustable
Action	Slow action
Safety Output Type	(2) N.C.
Housing Size	59 x 158 x 42mm
Body Material	Die-cast aluminum
Head Material	Plastic
IP Rating	IP66
Connection	(3) 1/2in NPT cable entries

Agency Approvals

UL Listed File #	e189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	176294
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SDM2K61W02.pdf>
See store item page for other formats.