

SDN12362508PL Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 36 x 25 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDN12362508PL>

Technical Specifications

Brand	Wiegmann	Integral Mounting Feet	Yes
Item	Disconnect enclosure	Material	Carbon steel
Slope Top	No	Color	ANSI 61 gray
Vented	No	Finish	Powder coat
NEMA Rating	12/13	Cover Type	Single-door
Disconnect Mounting	Right flange	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	36 x 25 x 8in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	36.00in	Latch Type	2-point padlocking handle
Enclosure Width	25.38in	Padlockable	Yes
Enclosure Depth	8.88in	Keylocking	No
Mounting	Wall	Subpanel	Purchase subpanel separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SDN12362508PL.pdf>
See store item page for other formats.