

# SDN12363212PL Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 36 x 31 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDN12363212PL>

## Technical Specifications

Brand	Wiegmann	Color	ANSI 61 gray
Item	Disconnect enclosure	Finish	Powder coat
Slope Top	No	Cover Type	Single-door
NEMA Rating	12/13	Hinge Type	Continuous hinge
Disconnect Mounting	Right flange	Number of Hinges Per Door	1
Nominal Enclosure Dimensions	36 x 31 x 12in (HxWxD)	Latch Type	2-point padlocking handle
Enclosure Height	36.00in	Padlockable	Yes
Enclosure Width	31.37in	Keylocking	No
Enclosure Depth	12.88in	Subpanel	Purchase subpanel separately
Mounting	Wall	For Use With	Most major brand disconnect switches and circuit breakers
Integral Mounting Feet	Yes	Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier
Integral Mounting Flange	No		
Dual Access	No		
Knockouts	No		
Material	Carbon steel		

## Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>